


BELSIL[®] DM 1000



Silicone Fluids (INCI)

is a linear, non-reactive, unmodified polydimethylsiloxane. is characterized by low surface tension and a high spreading coefficient. Due to their flexible polymer backbone, dimethicones have high permeability to gases (e.g. water vapor, oxygen), which allows respiration of the skin.

INCI Dimethicone



R = Me

Technical data

General Characteristics

Property	Condition	Value	Method
Aggregate state	-	liquid	-
Appearance	-	colorless, clear	-
Density	25 °C	approx. 0.97 g/cm ³	DIN 51757
Flash point	-	> 300 °C	ISO 2592
INCI name	-	Dimethicone	-
Ignition temperature	-	410 °C	EN 14522
Refractive index	25 °C	1.4035	-
Surface tension	25 °C	approx. 0.021 N/m	-
Viscosity, dynamic	25 °C	1000 mPa·s	DIN 53019
Viscosity, kinematic	25 °C	approx. 1000 mm ² /s	DIN 53019

These figures are only intended as a guide and should not be used in preparing specifications.

All the information provided is in accordance with the present state of our knowledge. Nonetheless, we disclaim any warranty or liability whatsoever and reserve the right, at any time, to effect technical alterations. The information provided, as well as the product's fitness for an intended application, should be checked by the buyer in preliminary trials. Contractual terms and conditions always take precedence. This disclaimer of warranty and liability also applies particularly in foreign countries with respect to third parties' rights.

Applications

- Eye Make-up
- Lip Make-up
- Make-up
- Make-up Foundation
- Skin Care
- Sun Care

Application details

is used in a broad range of personal care formulations as an emollient. It allows formulators to adjust spreadability and conditioning effects. Whitening and stickiness of cosmetic products can be reduced and skin feel can be optimized.

Packaging and storage

Storage

Maximum temperature allowed during storage and transportation: 50 °C The 'Best use before end' date of each batch is shown on the product label. Storage beyond the date specified on the label does not necessarily mean that the product is no longer usable. In this case however, the properties required for the intended use must be checked for quality assurance reasons.

Safety notes

Comprehensive instructions are given in the corresponding Material Safety Data Sheets. They are available on request from WACKER subsidiaries or may be printed via WACKER web site <http://www.wacker.com>.

QR Code BELSIL® DM 1000



For technical, quality or product safety questions, please contact:

Wacker Chemie AG, Gisela-Stein-Strasse 1, 81671 Munich, Germany
productinformation@wacker.com, www.wacker.com

The data presented in this medium are in accordance with the present state of our knowledge but do not absolve the user from carefully checking all supplies immediately on receipt. We reserve the right to alter product constants within the scope of technical progress or new developments. The recommendations made in this medium should be checked by preliminary trials because of conditions during processing over which we have no control, especially where other companies' raw materials are also being used. The information provided by us does not absolve the user from the obligation of investigating the possibility of infringement of third parties' rights and, if necessary, clarifying the position. Recommendations for use do not constitute a warranty, either express or implied, of the fitness or suitability of the product for a particular purpose.